

Home > Products > Product Feature Selector > Product Details

4-1734774-8 Product Details

 Share

 Print

 Email



PCI & PCI Express Connectors

PCI EXP 2.3L 164 POS BLK 30u"

4-1734774-8 

TE Internal Number: 4-1734774-8

Product Highlights [View All](#)

- Family Name = PCI Express
- PCB Mounting Orientation = Vertical
- 82 Dual Positions
- 164 Positions
- Housing Color = Black

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Family Name	PCI Express
PCB Mounting Orientation	Vertical
PCB Mount Style 	Through Hole
PCB Mount Retention Type	Pylon

Electrical Characteristics	
Voltage (VAC) 	50
Operating Voltage (VAC)	50
Current Rating (A)	1.1

Termination Features	
Termination Post Length (mm [in]) 	2.30 [0.091]

Dimensions	
Length (mm [in])	89.00 [3.504]
Width (mm [in])	8.80 [0.346]
Height (mm [in])	10.00 [0.394]
PCB Thickness, Recommended (mm [in])	1.60 [0.063]
PCB Thickness, Accepted (mm [in])	1.57 [0.062]

Body Features	
Ejector	Without
Number of Pylons	2
Pylon Material	Plastic
Weight (g [oz])	8.70 [0.307]

Contact Features	
Contact Plating, Mating Area, Material 	Gold (30)
Contact Base Material	Phosphor Bronze
Solder Tail Contact Plating	Matte Tin over Nickel (50)

Housing Features	
Housing Color	Black
Centerline (mm [in])	1.00 [0.039]
Housing Material	PA9T GF

Configuration Features	
Number of Dual Positions 	82
Number of Positions	164

Industry Standards	
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant
PCI Generation	II & III

Environmental	
Operating Temperature Range (°C)	-40 – +85

Operation/Application	
Pick and Place Cover	Without

Packaging Features	
Packaging Method	Tray

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

