

Loading...

2m 90° to 90° External Serial ATA Cable (6.6ft)

Hot-pluggable with transfer rates up to 6G

★★★★★

0 Reviews

- Product # : 10225
- Connector 1 : (1) eSATA 7-pin Male
- Connector 2 : (1) eSATA 7-pin Male
- Lengths :

6.6ft

3.3ft

In Stock, only 9 left to ship!

1

Add

VISA

MasterCard

AMERICAN EXPRESS

DISCOVER

PayPal

pay

Need It shipped today?

Place your order before the timer runs out!

08: 44: 55

print

share

chat

- Product Info
- ★ Customer Reviews
- Questions & Answers
- Distributors
- More Choices

- Description
- Certifications
- Specs

Product Description

With the right-angled connectors, this cable can connect at a more desired angle and is fortified to keep the cable lined up straight. So you'll see less cable bend and fatigue for longer cable life. eSATA provides more performance than current solutions and is hot-pluggable. You can now utilize shielded cable lengths up to 2 meters outside the PC to take advantage of the benefits the SATA interface brings to storage.

SATA is now out-of-the-box as an external standard, with specifically defined cables, connectors, and signal requirements. With eSATA, you get a robust and user-friendly external connection with high performance and cost-effective expansion storage. SATA 3.0 compatible with transfer rates up to 6 Gbps!

WARNING: Cancer and Reproductive Harm [www.P65Warnings.ca.gov](#)

Product Certifications



Product Specifications

Color :	Black
Length :	2.00 Meter

UPC :	757120102250
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.330 LB

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [▶](#) [b](#)



United States | Europe +
Copyright © 2019 C2G. All Rights Reserved

