Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
  - Middle Size
  - Large Size
  - ODVA
  - Accessory
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub



RCP5SM-SPG06M-SR7B30

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: Cat 5e
- Shielded: Plastic, Shielded
- Jacket Material: PVC
- Certificate: N/A

You must login first for view the price


Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type | Search



RJ, Middle Size,... RCP-5SAFFM-... -20°C ~ +80°C — − 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current: **1.5A**	Connector Type: **Overmolded**
Shielded: **Plastic, Shielded**	No. of Contacts: **N/A**
Connector Gender: **Plug**	Backshell: **Right Angle**
Mating Style: **Screw Thread**	IP Rating: **IP67**
Assembly Style: **N/A**	

More Options

People Also Bought



RCP5SM-SPG06M-... | MSBP-05BFFB-... | AB-BD03HL-BDBR-... | DCU-08AMEM-... | MSAS-12BFFM-...

Downloaded from Arrow.com.