




696640-1 Product Details

 Share

 Print

 Email



 Active

Ring and Spade Tongue Terminals

KIT-4,1/4,NI+RT555-.500X1.50

696640-1

TE Internal Number: 696640-1

Product Highlights

[View All](#)

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = SOLISTRAND
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	1/4 [M6]
Shape	RING-051
Heavy Duty	No
Finish	Tin

Termination Features

Wire/Cable Size (CMA)	190,000 – 231,100
-----------------------	-------------------

Dimensions

Stud Diameter (mm [in])	6.73 [0.265]
-------------------------	--------------

Body Features

Body Style	SOLISTRAND
Wire Range (mm [AWG])	100.00-125.00.0² [4/0]
Material	Copper

Contact Features

Terminal Shape	Ring Tongue
----------------	-------------

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

Brand	TE Connectivity
-------	-----------------

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)