

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020088](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway™ Rubber Hand Lamp with 100W Quick Open Guard and Reflector with Side Outlet, Cord Length 15.24m (50.0'), Cord Type 16/3 SOOW

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130102](#)
NEMA Configuration NEMA 5-15
Outlet Side
Overview [Hand Lamps](#)
Product Literature Order No 987650-8053
Product Name Super-Safeway™
Type Hand Lamps
UPC 78678879413
Woodhead Yes

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 101.60mm (4.000")
Duty Industrial
Guard Included No
Guard Type Metal Wire
Height 374.65mm (14.750")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 240V

Material Info

Old Part Number 105UB163



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
ELV Not Reviewed

Search Parts in this Series

[130102](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION