

3100 03430001

(Home (/index.php?ci_id=3972&la_id=1) : Products (/products) : Active Product Family 10-Oct-2006 : Sensors : Thermostats : 3100)

Distributor Inventory

Input part number for stock availability



3100 Series Hermetic Thermostats

Actual product appearance may vary.

Narrow Your Search

Modify Your Search

Products

Technology

Industries Served

Sales & Service

Distributor Inventory

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	2.0 A/1.0 A/5.0 A/5.0 A
Voltage	120 Vac/240 Vac/30 Vac/30 Vdc
Operating Temperature	-29 °C to 260 °C [-20 °F to 500 °F]
Environmental Exposure Range	-62 °C to 288 °C [-80 °F to 550 °F]
Open Temperature	80.0 °C [176 °F]
Close Temperature	70.0 °C [158 °F]
Open Tolerance	3.3 °C [6 °F]
Close Tolerance	3.3 °C [6 °F]
Dielectric Strength	MIL-STD-202, Method 301; 1250 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Hermetic Seal	MIL-STD-202, Method 112; Cond. 1x10-5
Moisture Resistance	MIL-STD-202, Method 106
Housing Material	Steel housing hermetically sealed with glass-to-metal seal at terminal junction
Contact Material	Silver
Mounting	B215 fixed bracket
Series Name	3100

Product Search

Product Type:

☐ New Products Only

Industry:

Search Term: **Start Here ...****Search****My Links**

eCOM Login (/index.php?ci_id=50629&la_id=1)
Request Access to eCOM (/ecom access request)
Rep/AD Portal Login (/index.php?ci_id=50606&la_id=1)
Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1)
Sample Request (/samplerequest)
Digital U - HWL Learning Hub Login (/index.php?ci_id=50607&la_id=1)
Digital U - HWL Learning Hub Access Request (/index.php?ci_id=146099&la_id=1)
 <http://www.youtube.com/user/SensingAndControl>
Supplier Microsite (/index.php?ci_id=50631&la_id=1)
Supplier Microsite (/index.php?ci_id=44887&la_id=1)

Literature and Media

Data Sheets (/white paper and technical data sheets library)
Videos (/videos)
Literature (/literature)
Literature Request (/index.php?ci_id=50636&la_id=1)
White Papers (/whitepapers)
Application Notes (/application notes)
Application Demos (/index.php?ci_id=141383&la_id=1)
CAD Renderings (/cad renderings)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)
Technical Support (/index.php?ci_id=50609&la_id=1)
Global Sales & Service (/index.php?ci_id=50610&la_id=1)
Website Feedback (/index.php?ci_id=142628&la_id=1)

Terms & Conditions (/index.php?ci_id=2588&la_id=1)**Privacy Statement** (/index.php?ci_id=2589&la_id=1)**Site Map** (/sitemap)