

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE





NOTES1:

UL Standard

1.Rated voltage/current : 600V / 10A(01P)、300V / 10A(02P/03P)

2.Wire range : 20~16AWG

IEC Standard

1.

Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	4.0KV	4.0KV	4.0KV
Rate voltage(V)	320V	200V	200V
Rate current(A)	17.5A		

2.Wire range : 0.5~1.5mm²

NOTES2:

1.Dimension shall be interpreted per ASME Y14.5-2009

2.Pitch : 6.00mm, Poles : N=01~03P


3.Stripping length : 9~11mm

4.Operating temperature: -40°C~+130°C

5.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm					— ⌒ ▱
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10
								∠
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°

6.RoHS Compliance



PCB LAYOUT

DG2003 - 6.0 - XXP - 1Y - 01A (H)

(Series No.) (Pitch) (Poles) (Single Pitch) (Color):1.(Grey) 3.(Black) 01A-(Customer request) (RoHS)

DETACHED LISTS	PART NO.: /	DEGSON® 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
	APPD: /	NAME: DG2003-6.0-XXP-1Y-01A(H)	
	CHKD: /		
	DRFT: /	TITLE: CUSTOMER DRAWING	REV D0
	THIRD ANGLE PROJECTION	DRAWING NO.: /	SHEET 1/1
		MM (INCH) DO NOT SCALE DRAWING	SCALE 1:1

Downloaded from Arrow.com.