

Specification Sheet

Part Number: 151-00180



Head design contains clamping rails to provide full circumferential compression around bundles.

Bent tail allows for quick insertion into head.

Conn. Clip w/Oval Fir Tree, 0.6-6.0 mm Panel Thick, 6.2x12.2 mm Hole Dia, PA66HIRHS, Black, 1000/pkg

Article Number 151-00180

Type YCCFT62x122

Quantity Per pcs.

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Conn. Clip w/Oval Fir Tree, 0.6-6.0 mm Panel Thick, 6.2x12.2 mm Hole Dia, PA66HIRHS, Black, 1000/pkg

Global Part Name YCCFT62x122-PA66HIRHS

Length L (Imperial)	0.83
Length L (Metric)	21.08
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.63
Width W (Metric)	16.0
Height H (Imperial)	0.71
Height H (Metric)	18.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.244
Mounting Hole Diameter D Max (Imperial)	0.48
Mounting Hole Diameter D Max (Metric)	12.2

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)