



Kit size: 86,0 x 210,0
[3.39" x 8.27"]



7 sheets/kit



3 sheets/kit



1 sheet/kit



Customer drawing
/

TOLERANCES	
Label height :	±0,2
Label width :	±0,2
Web width :	±0,5
Vertical repeat :	±0,3*
Horizontal repeat :	±0,5*
Print positioning :	±0,5*
Left margin :	±0,5
Quantity :	0% +2%
* non accumulating	


THIS DRAWING IS A CONTROLLED DOCUMENT	
DIMENSIONS	TOLERANCES UNLESS OTHERWISE SPECIFIED
MATERIAL	FINISH
SEE TABLE	Gloss

REVISIONS

Rév.	Description	Visa	Date
A	Drawing creation	EL	27.01.22

CALIBRATION	
I.D. No.	_____
By	_____ Date _____
Due	_____

x 84 - Green



x 108 - Black



x 55 - Red

TOTAL : 247 labels

12, 36 or 55 labels/sheet
11 sheets/kit

TE PN: 2404500-1

All dimensions in mm/[inch]

Labels are centered on the liner except against indication

Overlamination: /					
Material :		White PVC			
Adhesive :		Permanent			
Liner:		Kraft			
DWN	EL / 27.01.22	DATE	 TE Connectivity		
CHK	EL / 27.01.22	DATE			
APVD	SET / 15.02.22	DATE			
PRODUCT SPEC		DATE			
TTDS-249		Part			
APPLICATION SPEC		DATE	CALIBRATION-LABEL-BK-247		
WEIGHT	25,5 g (étiqu)	SIZE	CAGE CODE	TE DRAWING	RESTRICTED TO
SCALE	NTS	A4	FB1U7	CALIBRATION-LABEL-BK-247_20220131	
CUSTOMER DRAWING			SHEET 1 OF 1		REV A

- Kiss cut
- Die cut
- Back slit
- Adhesive cut
- Perforation
- 45° die cut
- 2 kiss cut enductions