












Max. Temperature: 260° during 10 seconds.

0955 369 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)			
0955 369 3812 741	1	4-40 UNC					
0955 369 6811 741	2	M3					
0955 369 6812 741	2	4-40 UNC					
0955 369 7811 741	3	M3					
0955 369 7812 741	3	4-40 UNC					
Part number	PL	Nut	Index designation				
 All Dimensions in mm Original Size DIN A 3			Techn. Character.		Free size tolerances		
					2 : 1	D-Sub SMT, 25 poles Male, Straight with nuts and ground pins	
			Detail.	Dat. 25-Oct-11			Name Johnson.S
			Insp.	17-Nov-11			Steven.W
			Stand.	17-Nov-11			Steven.W
EC04070	17-Nov-11	Johnson.S	Zhuhai HARTING Limited			TB 09 55 369 x81x	Page 1 / 2
Mod.	Dat.	Name					
			Sub.				



 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
				Dat.	Name	Scale	D-Sub SMT, 25 poles Male, Straight with nuts and ground pins	
			Detail.	25-Oct-11	Johnson.S			
			Insp.	17-Nov-11	Steven.W			
			Stand.	17-Nov-11	Steven.W			
			Zhuhai HARTING Limited 			TB 09 55 369 x81x		Page 2 / 2
EC04070	17-Nov-11	Johnson.S				Sub.		
Mod.	Dat.	Name						