

HDMI Display-Side Wallplate with Active Signal Booster, White (F/F)

MODEL NUMBER: **P166-001-A**



Highlights

- Extend a 1080p (24Hz) HDMI signal up to 150-ft. (45.72 m) from the source
- When extending a 1080p (24Hz) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio

Package Includes

- HDMI Display-side Wallplate w/Signal Booster

Description

Tripp Lite's P166-001-A HDMI Display-side Wallplate with Signal Booster increases the distance a 1080p (24Hz) signal can be transmitted beyond the recommended 16-ft. (4.88 m.). It supports video resolutions up to 1080p, and a maximum distance of 150-ft. (45.72 m) from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p (24Hz) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100-ft. (30.5 m) are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable. Simply connect the longer cable between the source and the P166-001-A, and the shorter cable (16-ft. (4.88 m) or less) between the adapter and the monitor. Software or drivers are not required. HDCP compliant.

Features

- Cleans up Home Theater installations by hiding HDMI Cables
- Wallplate is the size of a standard electrical outlet
- Extend a 1080p (24Hz) HDMI signal up to 150-ft. (45.72 m) from the source
- Use P568-Series HDMI cables in most applications
- When extending a 1080p (24Hz) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100-ft. (30.5 m) are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- HDCP compliant
- No software or drivers required

Specifications

OVERVIEW

UPC Code	037332141033
Product Type	Signal Booster
Accessory Type	Wall Plate
Technology	HDMI
VIDEO	
HDR Support	No
3D Video Supported	No
Maximum Signal Range (ft)	150
Maximum Signal Range (m)	46
INPUT	
Bus Powered	No
POWER	
Power Over Cable (PoC) Support	No
PHYSICAL	
Color	White
Number of Displays	1
Form Factor/Mounting Options	Wallplate
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
COMMUNICATIONS	
EDID Compatible	No
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)

FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
Driver Required	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty