

[ABOUT KEYSTONE ELECTRONICS](#)[CUSTOM CAPABILITIES](#)[VIEW / DOWNLOAD E-CATALOG](#)[PART BUILDER SYSTEM](#)[CALENDAR OF EVENTS](#)[NEWS, ADS AND VIDEOS](#)[DISTRIBUTOR LOCATOR](#)[ON-LINE ORDERING](#)[CHECK DISTRIBUTOR STOCK](#)

PRODUCT CATALOG:

[ALL PRODUCT CATEGORIES](#)[BATTERY & COIN CELL HOLDERS,
CONTACTS & CLIPS](#)[FUSE CLIPS & FUSE HOLDERS](#)[HANDLES FOR INSTRUMENTATION](#)[I-CLAMPS - IDC CONNECTORS](#)[LED SPACERS & LENS CAPS](#)[METAL KEY-PAD DOME SWITCHES](#)[MULTI-PURPOSE HARDWARE](#)[PANEL HARDWARE](#)[PC BOARD HARDWARE](#)[PLUGS, PINS, JACKS & SOCKETS](#)[QUICK-FIT TERMINALS](#)[SCREW TERMINALS & TERMINAL
BLOCKS](#)[SCREWS](#)[SPACERS & STANDOFFS](#)[TERMINALS & TERMINAL BOARDS](#)[TEST POINTS, TIPS, PROBES,
JUMPERS AND CLIPS](#)[ISO 9001:2015 CERTIFIED](#)[ROHS COMMITMENT](#)[REACH DECLARATION](#)[CONFLICT MINERALS DECLARATION](#)[DISTRIBUTOR LOG-IN CENTER](#)[PRODUCT WARRANTY INFORMATION](#)

SMT-Top & Side Entry Female Quick-Fit on T&R W/ Kapton Tape P/N 3586KTR

[Download: PDF](#)[Download: STEP](#)[ADD TO SAMPLE CART](#)

Part Number: 3586KTR

- **Current Rating:** 30 AMP
- **Fuse Entry:** Vertical
- **Fuse Reference:** Littelfuse ATO 257 series / Bussmann ATC series / APR / Littelfuse 891,897 series / Bussmann ATM-LP series / APS / Littelfuse 297 or 997 series / Bussmann ATM series / APM or equivalent
- **Fuse Size:** Standard
- **Fuse Type:** Automotive
- **Material:** .016 [0.40] Brass, Tin-Nickel Plate
- **Mounting:** SMT
- **Packaging:** Tape and Reel (per the ANSI/EIA-481 standard)
- **Style:** CLIP
- **UL Recognized:** Yes - (USA & Canada) E201546
- Kapton Tape added to top surface for vacuum pick and place. Tape must be removed prior to use.



Cat No. 3586TR is UL recognized as an Auto fuse clip only.

[Check Distributor
Stock](#)[BACK TO PREVIOUS PAGE](#)