



**Part Number :** [1300970235](#)

**Product Description :** Deluxe Cord Grips Strain Relief, 1-1/2" NPT, Straight Male, Cable Diameter 22.23-25.40mm (.875-1.000")

**Series Number :** 130097

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 36475



---

## Documents and Resources


### Drawings

[1300970235 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(b)-II per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130097
Description	Deluxe Cord Grips Strain Relief, 1-1/2" NPT, Straight Male, Cable Diameter 22.23-25.40mm (.875-1.000")
Hazardous Locations	Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
NEMA Rating	NEMA 4
Product Name	Deluxe Cord
Type	Strain Relief Grip
UPC	78678836475

#### Agency

CSA	LR32159
UL	E76954

#### Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	22.23-25.40mm (.875-1.000")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Aluminum
Material - Grip	Stainless Steel
Mesh Length	N/A

Net Weight	264.265/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	1 1/2" NPT

---

This document was generated on Apr 26, 2026