



This document is the property of Amphenol Corporation and is loaned to the customer for use in the design, development or testing of products or in part, for manufacturing or sale by anyone other than Amphenol Corporation. It shall be returned to Amphenol Corporation at the time of delivery of the product or at the time of sale or in any other manner in which it is used.



REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
A	HK	PRELIMINARY RELEASE	01/18/03	Y.M.LEE

TABLE 1

CONNECTOR SIZES	AVERAGE MATING FORCE (POUNDS)
14	5
24	8
36	12
50	15
64	19

SPECIFICATIONS:

- 1) SOLDER CUP CONTACT: TO ACCOMMODATE 22-30 AWG SOLID AND 24-30 STRANDED CONNECTOR WIRES.
- 2) DIELECTRIC: DIALYL-PHTHALATE PER MIL-M-14F TYPE MDG UL-94V0
- 3) CONTACT MATERIAL: COPPER ALLOY
- 4) CONTACT: 20 MICRO-INCHES MIN. GOLD MATING AREA: GOLD FLASH ON TAIL AREA. 50 MICRO-INCHES MIN. NICKEL UNDERPLATING ALL OVER.
- 5) SHELL MATERIAL: ZINC PLATED STEEL WITH CLEAR CHROMATE COATING
- 6) CURRENT CAPACITY: 5 AMPS/CONTACT
- 7) VOLTAGE RATING: 700 VOLTS D.C. AT SEA LEVEL
200 VOLTS D.C. AT 70,000 FEET
- 8) INSULATION RESISTANCE: >5000 M OHM
- 9) DIELECTRIC WITHSTANDING VOLTAGE: 1200 VAC (RMS) AT SEA LEVEL
- 10) CONNECTOR MATING FORCE: REFER TO TABLE 1.

- 11) CONTACT RETENTION FORCE: 2 LBS MAX.
- 12) DURABILITY: 250 CYCLES MIN.
- 13) VIBRATION: NO INTERRUPTIONS < 1u SEC.
- 14) OPERATING TEMPERATURE: -55°C TO +105°C (-67°F TO +221°F)

CUSTOMER INFORMATION DRAWING

ITEM NO	PART OR IDENTIFICATION NO	NAME/CLATURE OR DESCRIPTION	CITY REQ'D
PARTS LIST			
UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. INCHES X +/- 0.020 XX +/- 0.010 XXX +/- 0.005 FRACTIONS +/- 1/16" ANGLES +/- 1° FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES (METRIC) (MM)		APPROVAL DRAWN Y.M. LEE CHECKED Y.M. LEE DATE 01/18/03 01/18/03 DRAWING FILE: DRAWING/007/C5760360.DWG ANGLE OF PROJECTION FIRST ANGLE SCALE NONE	Amphenol Amphenol Corp. Asia Limited Manufacturing Operation TITLE 36 CONTACT CABLE RECEPTACLE. ASSY WITH SPRING LATCH & MODIFIED BACK SHELL(MINI. RIBBON) SIZE A3 DRAWING NO. C57-60360 REV. A SHEET 1 OF 1