


Copyright FCI.

FCIconnect.com

PRODUCT NUMBER	PITCH
EZxx71x000J0G	5.00 mm







Material:
- Item ⓐ Terminal(housing): Thermoplastic (UL94V-0)
- Item ⓑ Clamp: Brass(CuZn) Ni plated
- Item ⓒ Female contact: PhBz Tin plated
- Item ⓓ Terminal Screw: Steel zinc plated.

Electrical: cULus
- Voltage rating: 300 V
- Current rating: 15 A
- Wire range:
- Solid wire(AWG):12-22
- Stranded wire(AWG):12-22
- Torque: 4.3 Lb-In
- Screw:M3
- Wire strip length:7-8 mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval:

N=NUMBER OF POLES

Dim L=N×5.0+0.3
Dim B=(N-1)×5.0
Dim C=N×5.0

POLES	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.25
19P-24P	±0.30

PART NO.: EZ xx 71 x 0 00J0 G

Solid block
No. of poles
02 2 poles
03 3 poles
... ...
24 24 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant (lead<4%) In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family: TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: TERMINAL BLOCK PLUGGABLE PLUG,WITHOUT FLANGE
				angles	linear: X.±0.5 / X.X±0.3 / X.XX±0.1	MM	
				X°±1°		scale	
				dr EVIN ZHONG 041814			dwg no: EZxx71x000J0G — sheet 1 of 1 — size A4
				engr EVIN ZHONG 041814			
				chr HANKE FENG 041814			type: CUSTOMER Drawing
				appd SHI JUN 041814			
sheet index	revision	A					
	sheet	1					

Downloaded from Arrow.com.