

PRODUCT NUMBER

67016-YXXLF

COLOR CODE
(AS AVAILABLE)

0=GREY
2=BLACK




INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 2

STYLE, SEE TABLE
(AS AVAILABLE)

STYLE	SIZE	DIM "F"
06	2x 3	12.18
08	2x 4	14.54
10	2x 5	17.08
12	2x 6	19.62
14	2x 7	22.16
16	2x 8	24.70
18	2x 9	27.24
20	2x10	29.78
24	2x12	34.86
26	2x13	37.40
30	2x15	42.48
34	2x17	47.56
40	2x20	55.18
44	2x22	60.26
50	2x25	67.88
60	2x30	80.58
64	2x32	85.66

EXTENDED RANGE

- TOOLING FEASIBILITY CONFIRMED
- SAMPLES ON DEMAND
- AVAILABILITY ON DEMAND



NOTES:

- MOLDING MATERIAL UNFILLED POLYESTER
FLAME RETARDANT PER UL-94-V0
- RoHS COMPATIBLE PRODUCT
 - LABELLING:
- MEETS PACKAGING SPECS AS PER GS-14-920
 - LEGAL STATEMENT: SEE GS-22-008
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO MANUFACTURING SOLDER PROCESS
 - PRODUCT MEETS WITH EU 2002/EG/95
- THIS PART SERIES IS NOT INITIALLY INTENDED FOR
AUTOMOTIVE APPLICATIONS. ADDITIONAL FEES ARE
CHARGEABLE FOR ANY ADDITIONAL QUALIFICATION AND
TEST REPORTS PERFORMED OUTSIDE THE SCOPE OF THE
STANDARD PRODUCT SPECIFICATIONS.
- UNLESS OTHERWISE APPROVED BY AMPHENOL, ALL PARTS
AND COMPONENTS ARE DESIGNED & BUILT ACCORDING TO
AMPHENOL'S SPECIFICATIONS WHICH ARE SUBJECT TO
CHANGE WITHOUT NOTICE.

mat'l. code SEE NOTE 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE III			
ltr	ecn no	dr	date	tolerances unless otherwise specified				 mm scale 1:1	title STRAIN RELIEF STANDARD				
F	F05-0255	LMU	05.09.28	angles	linear	.X ± 0.3							
G	F06-0270	LMU	06.09.12			.XX ± 0.15							
H	F06-0274	LMU	06.09.25			.XXX ± 0.05							
J	F-26819	JCA	17.04.26	dr	L.MULIN		05.09.28	Amphenol FCI	dwg no		sheet 1 of 1	size	
K	F-37268	DDE	20.06.03	engr	J.COMPAGNON		05.09.28		67016		A3		
L	F-55026	DDE	25.03.19	chr									
				appd	J.COMPAGNON		05.09.28						
sheet index		revision sheet								type CUSTOMER		Drawing	