
Downloaded from Arrow.com.

Customer Information Sheet

DRAWING No.: M20-976XXXX SHEET 2 OF 2	IF IN DOUBT - ASK	©	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm

NOTES:
1. RECOMMENDED PCB MOUNTING HOLE SIZE = Ø1.00mm.
2. ALL TOLERANCES ARE ±0.25mm UNLESS OTHERWISE STATED.
3. FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C001XX (LATEST ISSUE).

SPECIFICATION:
MATERIAL:
MOULDING:
06 & 22 = GLASS-FILLED POLYESTER UL94V-0, BLACK
42 & 46 = HIGH TEMP NLYON 6T UL94V-0, BLACK
PINS = BRASS
FINISH:
PINS:
06 = TIN/LEAD
22 = GOLD ON CONTACT AREA, TIN/LEAD ON TAILS
42 = GOLD ON CONTACT AREA, 100% TIN ON TAILS
46 = 100% TIN
ELECTRICAL:
CURRENT RATING = 3A MAX
CONTACT RESISTANCE = 25 mΩ MAX (GOLD), 30 mΩ MAX (TIN)
INSULATION RESISTANCE = 1,000 MΩ MIN
DIELECTRIC STRENGTH = 750V AC/DC
MECHANICAL:
DURABILITY = 300 OPERATIONS (GOLD), 50 OPERATIONS (TIN)
ENVIRONMENTAL:
TEMPERATURE RANGE = -40°C TO +105°C
PACKING:
BAG



ORDER CODE:
M20-976XXXX
No. OF WAYS
02 TO 40
FINISH:
06 = TIN/LEAD
22 = SELECTIVE GOLD + TIN/LEAD
42 = SELECTIVE GOLD + 100% TIN
46 = 100% TIN

NAME	ISS.	DATE	C/NOTE
JAE	10	18.03.05	8458

APPROVED:
CHECKED:
DRAWN: P. ALEXANDER
CUSTOMER REF.:
ASSEMBLY DRG:

HARWIN

HARWIN INC U.S.A.	HARWIN PLC U.K.	HARWIN PTE SINGAPORE
TEL: (812) 542 2540	TEL: 023 9231 4545	TEL: 65 6779 4909
FAX: (812) 542 2541	FAX: 023 9231 4590	FAX: 65 6779 3868

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.05mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
2.54mm PITCH DIL
VERTICAL PC TAIL PIN HEADER

DRAWING NUMBER:
M20-976XXXX

SHT 2 OF 2