



Non-Metallic Conduits

• HG-DC Double Slit

Control panels, machine building, plant construction and wherever retrofitting is a requirement.


Features and Benefits

- Can be opened and closed repeatedly
- Cables can be inserted laterally
- Abrasion resistant
- Free of halogen, sulphur and phosphorus
- Self-extinguishing to IEC 61386
- Colour: black



HelaGuard HG-DC double slit conduit is ideal for retrofitting.

MATERIAL	Polyamide 6 (PA6)
Operating Temperature	-40 °C to +120 °C
Flammability	UL94 V2
Specifications	IEC 61386



HelaGuard non-metallic conduit

TYPE	Nominal Ø	NW Ø	Outside Ø (OD)	Inside Ø (ID)	Min. Bending Radius (R)	Weight (g/m)	Reel Length	Colour	Article-No.
HG-DC11	11	8.5	11.5	6.2	45	23	50 m	Black (BK)	166-11800
HG-DC13	13	10	13.0	7.9	55	37	50 m	Black (BK)	166-11801
HG-DC16	16	12	15.8	10.3	60	41	50 m	Black (BK)	166-11802
HG-DC21	21	17	21.2	13.9	90	63	50 m	Black (BK)	166-11803
HG-DC28	28	23	28.5	20.5	105	94	50 m	Black (BK)	166-11804
HG-DC34	34	29	34.5	26.6	150	118	25 m	Black (BK)	166-11805
HG-DC42	42	36	42.5	34.8	170	193	25 m	Black (BK)	166-11806
HG-DC54	54	48	54.5	45.3	170	263	25 m	Black (BK)	166-11807

All dimensions in mm. Subject to technical changes.

Other reel lengths available on request. Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval.