



Roll over image to zoom in

20ft DisplayPort™ Cable with Latches 8K UHD M/M - Black

Connect the DisplayPort output of a computer to the DisplayPort input of a computer monitor and support a High Bit Rate (HBR) digital audio/video connection at up to a 8K resolution

★★★★★

4.8

14 Reviews

Product # : 54424

Connector 1 : (1) DisplayPort Male

Connector 2 : (1) DisplayPort Male

Lengths :

20ft1ft3ft6ft10ft15ft

+ show all lengths

414 In Stock & ready to ship!

1

Add

VISA

MasterCard

AMERICAN EXPRESS

Discover

PayPal

pay

Need it shipped today?
Place your order before the timer runs out!

06: 40: 42

print

share

chat

Product Description

This cable is an ideal solution for connecting the DisplayPort output of a laptop to a computer monitor which accepts a DisplayPort input. This cable carries a digital audio/video signal and the connectors feature latches which secure the cable in the port. Support of a High Bit Rate (HBR) bandwidth means that this cable can carry up to a 8K UHD (7680 × 4320) resolution. This cable meets the requirements of high performance applications.

• Download a PDF with the technical specifications of this product on the Support tab or view the technical specifications of this product on the Specs tab

Product Features

- Directly connect a DisplayPort output to a DisplayPort input
- Carries a digital audio/video signal
- Supports a High Bit Rate (HBR) bandwidth and resolutions up to a 8K UHD (7680 × 4320)

⚠ WARNING: Cancer and Reproductive Harm [www.P65Warnings.ca.gov](#)

Product Specifications

Color :	Black
Length :	20.00 Foot
UPC :	757120544241
Warranty :	Lifetime

Vendor :	C2G
Weight :	0.913 LB

•Download a PDF with the technical specifications of this product on the Support tab

Electrical Specifications

- Voltage Rating: 30v
- Conductor Resistance: @ 20°C max
- Insulation Resistance: 10M#/km
- Time Delay: 5.2ns/m (max)
- Attenuation:
5.02dB@100-450MHz 7.69dB@1GHz
12.595dB@2GHz 17.495dB@3GHz
22.395dB@4GHz 27.295dB@5GHz
32.195dB@6GHz 37.095dB@7GHz

Physical Specifications:

- Minimum Bend Radius: 73mm
- Approvals: CE
- Warranty: Lifetime

Conductor (5 Pair):

- Conductor: 32AWG (7/0.08TC)
- Insulation: FM-PE, ID:0.62±0.05mm
- Color: White/Black, White/Brown, White/Red, White/Green, White/Blue
- Drain: 1:32AWG (7/0.08TC)
- Shield: AL-Foil Wrap, Transparent Wrap

Conductor (5 Conductors):

- Conductor: 32AWG (7/0.08TC)
- Insulation: PP, ID:ø0.5±0.05mm
- Color: Red, Blue, Purple, White, Gray

Overall Cable:

- Jacket: PVC
- Shield: AL-Foil Wrap Braid, 85% Min Coverage
- Drain: 2:30AWG (7/0.10 BC)
- OD: 6.0±0.15

Product Support

Downloads

- Download the [technical specifications](#)

[About Us](#)

[Order History](#)

[Where To Buy](#)

[More](#) ▾

[Contact Us](#)

[OEM Solutions](#)

[Tech Support](#)

[More](#) ▾

[Connector Guides](#)

[ConnectXpress](#)

[Drivers & Manuals](#)

[More](#) ▾

Get help with [Chat](#)

Call C2G **800.506.9607**



United States | [Europe +](#)

Copyright © 2019 C2G. All Rights Reserved

