
2227303-1

ACTIVE

SFP, Cage, Operating Temperature Range -55 – 85 °C [-67 – 185 °F], Data Rate (Max) 4 Gb/s, 1 Ports, Port Matrix Configuration 1 x 1



TE Internal #: **2227303-1**
TE Internal Description: **CAGE ASSEMBLY, SFP, .140 SOLDE**

Pluggable I/O Product Type : **Cage**
Sealable : **No**
Operating Temperature Range : **-55 – 85 °C [-67 – 185 °F]**
Data Rate (Max) (Gb/s): **4**
Number of Ports : **1**

Add to List | Get Free Samples

Similar Products

Compatible Parts & Tooling

Free Shipping available on most items.

Unit Price (USD): **$2.43**

The online pricing may vary from your contracted price. Please login to your account for account specific pricing.

	Quantity	Unit Price
Packaging: Piece	1	$2.43076
Minimum: 1	50	$2.21485
Increments: 1	100	$2.15217

View More Pricing +

660 IN TE STOCK - SHIPS IMMEDIATELY

QTY: 1

Extended Price: $2.43

ADD TO CART

Documents | Features | Product Compliance

Product Drawings
SFP, 1X1 SINGLE PIECE CAGE, SOLDER PIN
ENG_CD_2227303_C4.Pdf
English

CAD Files
3D PDF
3D_CVM_CVM_2227303-1_C1.pdf
3D
Customer View Model
ENG_CVM_CVM_2227303-1_C1.3d_stp.zip
English
ENG_CVM_CVM_2227303-1_C1.2d_dxf.zip
English
ENG_CVM_CVM_2227303-1_C1.3d_igs.zip
English

Product Specifications
Application Specification
ENG_SS_114-13120_L.pdf
English
Product Specification
ENG_SS_108-1950_D_108-1950_D.pdf
English
Qualification Test Report
ENG_SS_501-128801_A_501-128801_A.pdf
English

Product Change Notification
View Product Change Notification
Login required to access product change notifications

SHOP OUR DISTRIBUTORS

North America | See all price breaks

Distributor	1	10,000	Buy
Avnet Electronics 18,889 in-stock	$1.599	$1.599	SHOP NOW
Arrow Electronics Inc. 2,867 in-stock	$1.615	$1.545	SHOP NOW
Online Components 975 in-stock		$1.150	SHOP NOW

View More Distributors (6)

We are here to help!
Get in touch with our product experts.

CHAT WITH US
EMAIL US
CALL US

REPORT PRODUCT DATA ERROR

Compatible Parts

All Compatible Parts (6)
Associated Parts (4)
Mating parts (2)

Filter By Specification

ASSOCIATED — 1367073-2 — SFP, Connector, .8mm [.031in].... From: 4.232 In-Stock — ADD TO CART

MATING — 1888901-1 — EMI Plug Dust Cover, Copper... From: 4.576 In-Stock — VIEW PRODUCT

ASSOCIATED — 1367073-1 — SFP, Connector, .8mm [.031in].... From: 0.867 In-Stock — VIEW PRODUCT

ASSOCIATED — 1367147-1 — Dust Cover, Black, Thermoplastic From: 1.365 In-Stock — ADD TO CART

ASSOCIATED — 1367147-3 — Dust Cover, Black, Thermoplastic From: 1.290 In-Stock — ADD TO CART

MATING — 1761394-1 — Dust Cover, Black, Thermoplastic From: 1.150 In-Stock — ADD TO CART

Products with Similar Specs

View All Similar Products

THIS PRODUCT

HIGH SPEED PLUGGABLE IO CONNECTORS & CAGES
2227303-1
SFP, Cage, Operating Temperature Range -55 – 85 °C [-67 – 185 °F]...
From $2.431 In-Stock
Pluggable I/O Product Type : **Cage**
Sealable : **No**
Operating Temperature Range : **-55 – 85 °C**
Data Rate (Max) : **4 Gb/s**
Number of Ports : **1**

Top Results

HIGH SPEED PLUGGABLE IO CONNECTORS & CAGES
1367629-2
SFP, Cage, .8mm [.031in] Centerline, Signal, Operating Temperature...
In-Stock
Pluggable I/O Product Type : **Cage**
Centerline (Pitch) : **.8 mm**
Sealable : **No**
Circuit Application : **Signal**
Operating Temperature Range : **-55 – 85 °C**

HIGH SPEED PLUGGABLE IO CONNECTORS & CAGES
2170167-1
SFP, Cage Assembly, Signal, Operating Temperature Range -55...
Non-Stocked
Pluggable I/O Product Type : **Cage Assembly**
Sealable : **No**
Circuit Application : **Signal**
Operating Temperature Range : **-55 – 105 °C**
Data Rate (Max) : **4 Gb/s**

HIGH SPEED PLUGGABLE IO CONNECTORS & CAGES
2170282-1
SFP, Cage Assembly with Integrated Connector, .8mm [.032in]...
Non-Stocked
Pluggable I/O Product Type : **Cage Assembly with Integrated Connector**
Centerline (Pitch) : **.8 mm**
Sealable : **No**
Circuit Application : **Signal**
Operating Temperature Range : **-5...**

Customers Also Bought

TE Part #: **2-179960-2**
PCB Mount Header, Vertical, 6 Position, 10.16 mm [.4 in]...
$17.923 per unit
Inventory: In-Stock
Add To Cart

TE Part #: **1-207119-0**
PCB Mount Header, Vertical, 4 Position, 5 mm [.197 in]...
$22.339 per unit
Inventory: In-Stock
Add To Cart

TE Part #: **H834KBYA**
34K ohm, Thin Film, Precision Resistor, .1 %, .25 W, ±15...
View Product

TE Part #: **2169797-4**
4 Position, PCB Mount Header, Board-to-Board...
View Product

Feedback

© 2026 TE Connectivity. All Rights Reserved.

Downloaded from Arrow.com.

Downloaded from Arrow.com.