



Part Number : [191930330](#)

Product Description : VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton

Series Number : 19193

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : H-381-14



Documents and Resources

Drawings

[191930330 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755052008

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	21.319/g
Packaging Type	Carton
Stud Size	1/4" (M6)

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	15.37mm max.
Wire Size (AWG)	1/0
Wire Size mm ²	50.00

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900011</u>
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	<u>192940008</u>
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG	<u>640038070</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

This document was generated on May 27, 2026