MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
1CH45-RB



CIRCUIT DIAGRAM









ANSI Y14.5M–1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT 5 OZ MAX

CHARACTERISTICS

OPERATING FORCE	6 - 12 LBS
FULL OVERTRAVEL FORCE	30 LB MAX
RELEASE FORCE	4 LB MIN
PRETRAVEL	.030 MAX
DIFFERENTIAL TRAVEL	.010 MAX
OVERTRAVEL	.100 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
2X S P D T

LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	4	4
IND	2	2
MOTOR	4	

NOTES
1 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 3
2 CIRCUIT DIAGRAM, CATALOG LISTING AND MICRO IDENTIFICATION PERMANENTLY MARKED ON SIDE OF SWITCH
3 - ALL EXPOSED PARTS ARE CORROSION RESISTANT
4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
5 - NO CHANGE WILL BE MADE IN CONSTRUCTION OR MATERIAL WITHOUT PRIOR APPROVAL OF GENERAL ELECTRIC
6 HARDWARE MAY BE FURNISHED UNASSEMBLED PER MIL-PRF-8805
7 MAJOR POLARIZING KEY OF CONNECTOR TO BE IN LINE WITH THE BUSHING KEYWAY WITHIN ±15°

X37943-CH

REPLACES PR-888

RELEASE NO. 7 JAN 02

CATALOG LISTING 1CH45-RB

ISSUE M 13 PAGE 1 OF 1

CHECK SAV

CHECK 7 JAN 02

DRAWN CSL 7 JAN 02

RASTER

REVISIONS

A	204664	CSL 7 JAN 02
B	0012945	12 MAY 05

Downloaded from Arrow.com.