



MRJE3404 Product Details

[Share](#) [Print](#) [Email](#)



Rotary Switches

MRJE3404

MRJE3404

TE Internal Number: 1825537-3

Active

Product Highlights [View All](#)

- 4 Positions
- Angle of Throw = 15.00 °
- Actuator Style = Long Thin Knob
- Code Type = 3 Poles
- Straight Mount Angle

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

[Feedback](#)

[Documents](#)

[Features](#)

[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Angle of Throw (°) 15.00

Actuator Style Long Thin Knob

Code Type 3 Poles

Mount Angle Straight

Product Series MRJE

Electrical Characteristics

Contact Rating 0.4VA

Contact Features

Solder Tail Contact Plating Gold over Nickel

Contact Base Material Brass

Housing Features

Housing Material Epoxy

Configuration Features

Number of Positions 4

Industry Standards

RoHS/ELV Compliance RoHS compliant, ELV compliant

Lead Free Solder Processes Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

RoHS/ELV Compliance History Always was RoHS compliant

Other

Brand Alcoswitch

Comment Fixed

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

