

Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

Power Extension Cord, Locking C13 to C14 PDU Style - 10A, 250V, 18 AWG, 2 ft. (0.61 m)

MODEL NUMBER: P004-L02



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your current power connection by 2 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other EquipmentThis IEC-320-C14 to IEC-320-C13 cable is an ideal replacement for a missing or worn-out computer power extension cord. Designed for data center and server room applications that do not require a higher-gauge cable, this UL-listed C14 male to C13 female cord can be used to power a computer, printer or monitor; attach a server or drive to a UPS system or PDU; or extend a current connection up to 2-ft. (0.61 m).

Locking Connector Helps Prevent Accidental Disconnection and Expensive DowntimeHaving a cable come loose accidentally can mean the loss of power and costly downtime. The P004-L02's locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Designed to Keep Your Equipment Connected a Long Time without StressThe SJT cable jacket is accentuated with integral strain relief, which gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Lifetime WarrantyThe P004-L02 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332218162

Highlights

- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Recommended for connecting power to computers, servers and other peripherals
- Adds 2-ft. (0.61 m) to your current power connection to provide more flexibility in placing devices
- Integral strain relief helps cable and connectors move freely without stress or cracking
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend a current power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-L02 C14 Male to C13 Female Power Cable, 2-ft. (0.61 m)

Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	10.00 x 7.09 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.01 x 1.27
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13 - LOCKING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No



1000 Eaton Boulevard
Cleveland, OH 44122
United States

High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.