

BIT E6,3 0,5X3,0X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Accessories, Screwdriver insert
Order No.	9024000000
Type	BIT E6,3 0,5X3,0X70
GTIN (EAN)	4008190852634
Qty.	5 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-02-12
Alternative product	2748910000

Creation date March 17, 2021 7:24:43 AM CET

Catalogue status 12.03.2021 / We reserve the right to make technical changes.

BIT E6,3 0,5X3,0X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	8.7 g	Weight	9 g
Width	70 mm	Width (inches)	2.756 inch

Technical data

Description of article	Bit with slotted blade, 0.5 x 3 x 70
------------------------	--------------------------------------

Electric screwdriver

Weight	9 g
--------	-----

Screwing tools

Blade length	70 mm	Blade thickness (A)	0.5 mm
Blade width (B)	3 mm	Form	E 6.3 DIN 3126, Slotted

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-04-90
ECLASS 11.0	21-04-42-04		

Approvals

ROHS	Conform
------	---------