



Part Number : [936012237](#)
Product Description : GWconnect STD -
Standard, Cover, Die-cast Aluminum, with 1
Lever, without Gasket, Size 16A «66x16», Grey
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7816.4595.0




Documents & Resources

Drawings
[936012237_sd.pdf](#)

3D Models and Design Files
[936012237_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect STD - Standard, Cover, Die-cast Aluminum, with 1 Lever, without Gasket, Size 16A «66x16», Grey
Comments	With nylon wire tether line.
Component Type	Cover
IP Rating	IP66
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191878928

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Component Size	16A «66X16»
Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum

Material - Lever	Stainless Steel
Net Weight	63.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	N/A
Thread Type	N/A

Use with Part(s)

Description	Part Number
Use With	Size 16A «66x16» Hoods with 2 Pegs

This document was generated on Nov 10, 2024