

Part Number : [936000044](#)

Product Description : Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg36 Thread

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands


Engineering Part Number : 7000.6846.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg36 Thread
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 24.0, 27.00, 30.00, and 33.00mm internal diameters.
IP Rating	IP66
Product Name	Heavy-Duty Connectors
UPC	887191826165

Physical

Cable Diameter	23.50-32.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	112.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg36
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
-------------	-------------

Use With	Enclosures Size A and B metal type
----------	------------------------------------

This document was generated on Apr 12, 2026