



Part Number : [451410410](#)
Product Description : MultiCat-to-MultiCat
High-Power Off-the-Shelf (OTS) Cable
Assembly, Female, Single Row, 1.0m Length, 8
AWG, 4 Circuits, Key A, Black
Series Number : 45141
Status : Active
Product Category : Power and Signal Cable
Assemblies
Engineering Number : KAB2543L1V01




Documents & Resources

- Drawings**
[Drawing 451410410_sd.pdf](#)
- 3D Models and Design Files**
[3D Model 451410410_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

- [Multiple Part Product Compliance Statements](#)
- Eu RoHS
 - REACH SVHC
 - Low-Halogen
- [Multiple Part Industry Compliance Documents](#)
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	45141
Description	MultiCat-to-MultiCat High-Power Off-the-Shelf (OTS) Cable Assembly, Female, Single Row, 1.0m Length, 8 AWG, 4 Circuits, Key A, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MultiCat-to-MultiCat
Product Family	MultiCat Power Connectors with Precision-Machined Contacts
Product Name	MultiCat
Type	Discrete Wire Assembly, High Reliability Assembly
UPC	191128292450

Electrical

Current - Maximum per Contact	40.0A
Voltage - Maximum	1000V AC

Physical

Cable Length	1.0m
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy

Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold
Material - Resin	PEI
Net Weight	443.700/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	7.40mm
Plating min - Mating	0.100µm
Plating min - Termination	0.200µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10669
Wire Insulation Diameter	4.03mm-5.84mm
Wire Size (AWG)	8

Mates With / Use With

Mates with Part(s)

Description	Part Number
MultiCat High-Power Inline Plug Housing, 4 Circuits, Black, Key A	<u>2018400040</u>
MultiCat High-Power Vertical Header, 4 Circuits, Key A, Black	<u>2018421040</u>
MultiCat High-Power Right-Angle Header, 4 Circuits, Key A, Black	<u>2018431040</u>

This document was generated on Mar 27, 2024