

bel

ENGDE简中

BEL GROUPS

PRODUCTS

INDUSTRIES

RESOURCES

CONTACT US

Home / Bel Magnetic Solutions / 1xN Port ICMs



belMAGNETIC SOLUTIONS



# G27-122T-015

DESCRIPTION

SUPPORT

REQUEST QUOTE

DOCUMENTS

1X1 | 10G | -40 to 85°C | 4PPoE 60W | GY/GY | Tab Up

|                       |               |
|-----------------------|---------------|
| Brand                 | Bel Magnetics |
| Number of Ports       | 1X1           |
| Speed                 | 10GBASE-T     |
| LED                   | Yes           |
| LED Type              | GY/GY         |
| Height Profile        | Standard      |
| Port Configuration    | Tab Up        |
| Operating Temperature | -40 to 85°C   |
| EMI Tabs              | YES           |
| PoE Rating            | 4PPoE 60W     |

Tech Help

## Products

Cable Assemblies

Circuit Protection

Connectors

Linear Transformers

Magnetic Solutions

Power Solutions

See All

## Bel Groups

Bel Fuse-Circuit Protection

Bel Magnetic Solutions

Bel Power Solutions

Cinch Connectivity Solutions

CUI, Inc.

Signal Transformer

Stewart Connector

TRP Connector

## Information

Contact Us

Privacy Statement

Bel GDPR Notice

## Connect with Us







## Explore Bel

About Us

Bel Extranet

Careers

Investors

News Room

Copyright © 2019, Bel Fuse Inc. All Rights Reserved.

ECIA MEMBER

Supporting The Authorized Channel

Downloaded from [Arrow.com](#)