

**RSV1,6 ZE24 BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

**For frequent load changes: the "trailer coupling" for plug-in connectors.**

The strain relief can do more than just relieve the strain on conductors:

Simply clip onto the plug and

- bundle conductors
- guide cables
- use as a connection and disconnection aid

No damage to the connecting points, clear, tidy wiring and easy to handle.

User advantages: permanent heavy-duty connections for harsh industrial environments and convenient operation ensure improved system availability.

**General ordering data**

|              |                                                                               |
|--------------|-------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, Accessories, Strain relief, black, Number of poles: 24 |
| Order No.    | <a href="#">1563100000</a>                                                    |
| Type         | RSV1,6 ZE24 BK BX                                                             |
| GTIN (EAN)   | 4008190051167                                                                 |
| Qty.         | 20 pc(s).                                                                     |
| Product data |                                                                               |
| Packaging    | Box                                                                           |

Creation date May 23, 2025 5:56:23 AM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

## RSV1,6 ZE24 BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 11.55 g |
|------------|---------|

## Material data

|                                       |          |                                       |          |
|---------------------------------------|----------|---------------------------------------|----------|
| Insulating material                   | PA       | Colour                                | black    |
| Colour chart (similar)                | RAL 9011 | Contact material                      | Cu-alloy |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C    |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C   |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C   |

## Rated data acc. to IEC

|                         |                        |
|-------------------------|------------------------|
| tested acc. to standard | IEC 60664-1, IEC 61984 |
|-------------------------|------------------------|

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 209 mm |
| VPE width | 144 mm | VPE height | 72 mm  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002943    | ETIM 7.0    | EC002943    |
| ETIM 8.0    | EC002943    | ETIM 9.0    | EC002943    |
| ETIM 10.0   | EC002943    | ECLASS 9.0  | 27-44-04-92 |
| ECLASS 9.1  | 27-44-04-92 | ECLASS 10.0 | 27-44-04-92 |
| ECLASS 11.0 | 27-46-04-02 | ECLASS 12.0 | 27-46-04-02 |
| ECLASS 13.0 | 27-46-04-02 | ECLASS 14.0 | 27-46-04-02 |
| ECLASS 15.0 | 27-46-04-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Important note

|                |                                                                                                                                                                                                                                                                                                                            |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
| Notes          | <ul style="list-style-type: none"> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul>                                                                                                                                                                   |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

Creation date May 23, 2025 5:56:23 AM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

## RSV1,6 ZE24 BK BX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity

[Declaration of the Manufacturer](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[MB DEVICE MANUF. EN](#)

[FL 72H SAMPLE SER EN](#)

[PO OMNIMATE EN](#)

[PO OMNIMATE EN](#)

**RSV1,6 ZE24 BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Natural**

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

|            |                            |                                               |
|------------|----------------------------|-----------------------------------------------|
| Type       | CB 140/3,5 NC              | Version                                       |
| Order No.  | <a href="#">1278700000</a> | Cable ties, 3.5 x 140 mm, Polyamide 66, 180 N |
| GTIN (EAN) | 4008190155759              |                                               |
| Qty.       | 100 pc(s).                 |                                               |