



LEV200AKANA Product Details

[Share](#) [Print](#) [Email](#)

Active

Contactors

LEV200AKANA=RELAY, SPST-NO

LEV200AKANA
TE Internal Number: 8-1618388-3
[Product Highlights](#) [View All](#)

- Contactor Type = Sealed
- LEV200 Series
- DC Actuating System
- 1 Poles
- Contact - Arrangement = 1 Form X, SPST-NO-DM

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

[Feedback](#)
[Documents](#) [Features](#) [Compliance](#)
Please Note:
Use the Product Drawing for all design activity

Product Type Features

Contactor Type Sealed

Terminal Configuration 10-32 Stud

Electrical Characteristics

Actuating System DC

Contact Rating 500A

Coil - Rated Voltage (VDC) 72

Termination Features

Coil Termination Wire

Dimensions

Coil Wire Length (mm [in]) 390 [15.3]

Body Features

Torque 80 in-lbs

Mount Type Bottom Mount

Contact Features

Number of Poles 1

Configuration Features

Contact - Arrangement 1 Form X, SPST-NO-DM

Auxiliary Switch Contact Arrangement None

Industry Standards

RoHS/ELV Compliance RoHS compliant, ELV compliant

Lead Free Solder Processes Not relevant for lead free process

RoHS/ELV Compliance History Always was RoHS compliant

Packaging Features

Packaging Method Individual

Other

Series LEV200

Brand Kilovac

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)
[View Part in Product Feature Selector](#)
[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

