

Representative Image

Catalog No. F9019

Description: NON-INS FERRULE 10, 6 MM2, LG .472

UPC No 786210335971

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Ferrule, Length .472 Inches/12mm, Inner Diameter .138 Inches/3.5mm, Outer Diameter .185 Inches/4.7mm, Conductor Size 10 AWG/6mm2, Copper, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.

Specifications

Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E489056

Dimensions

Wire Size	10 AWG

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000005 Cable end sleeve
Construction type	Standard
Nominal cross section	6 mm²
Insulated	N
Colour	None
Material	Copper
Surface protection	Tinned
With identification flag	N

by ABB

Downloaded from Arrow.com.

ETIM	EC000005 Cable end sleeve
Reel packaging	N
AWG size	10

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	260371	622801	N/A	2708699	N/A
UL	E489056	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.