


R2LC-4.0-RGB



ORCAdapt Flexible Light Pipe System, 2mm. Fiber Optic Core, 5.1mm. Dia. Low Profile Lens, 4.0in. Length, Tri-Color Rectangular RGB LED

FEATURES

VALUE ADDED

CHECK STOCK

- High Intensity Tri-Color LED, Red(4000mcd), Green (5000mcd), Blue (400mcd)
- 5.1mm. Diameter Low Profile Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Front Panel Mount Lens

**Enclosure Hardware****LED Indicators****LED Lighting****New Products****Locate a Distributor / Sales REP****Quality Assurance / RoHS****Product Info Center****Terms & Conditions****My Bivar**