




5.0

5 Reviews



5.0

5 Reviews

 Need Help?[Browse All Products](#) | [Cat5e / Cat6 / Cat6a](#) | [Cat6](#) | [Cat6 Snagless Patch Cables](#) Roll over image to zoom in

3ft Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Green

Snagless design for network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications.



5.0

5 Reviews

Product # : 27171

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Colors :

 Green Red Blue[+ show all colors](#)

Lengths :

3ft


0.5ft

1ft

2ft

4ft

5ft

[+ show all lengths](#)4,238 In Stock & ready to ship! 

Add



Need it shipped today?

Place your order before the timer runs out!



07:21:57

 print  share  chat Product Info Customer Reviews Questions & Answers Distributors More Choices

Description

Features

Certifications

Specs

Uses

Support

Product Description

For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Product Features

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

**WARNING:** Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Green
Length :	3.00 Foot
Jacket Rating :	Standard Non-Rated
UPC :	757120271710
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.120 LB

Electrical Characteristics

- Conductor DC Resistance - 9.38Ω/100m (maximum)
- Impedance - 100Ω
- Capacitance - 5600pf/100m
- Propagation Delay - 545ns/100m (maximum)
- Delay Skew - 45ns/100m (maximum)

Physical Characteristics

- Wiring Scheme - T568B
- Standard: Category 6 TIA/EIA-568-B-2.1, draft 9
- Connector: 50 micron gold-plated RJ45
- Temperature Rating - 60°C
- Voltage Rating - 30V
- Approvals - RoHS Compliant
- Warranty - Lifetime
- Package Type - Polybag

Conductor (Qty. 4 twisted pair)

- Conductor Type - 24AWG (7/0.20), Stranded Bare Copper
- Insulation - H-D PE
- Diameter - 0.98 ± 0.05mm
- Colors - Blue, Blue-White, Orange, Orange-White, Green, Green-White, Brown, Brown-White

Connector Type (Qty. 2)

- Connector Type - 8P8C (RJ45)
- Gender - Male
- Connector Material - Polycarbonate
- Contact Material - Copper Alloy, Gold Plating - 50µm
- Hood Material - Molded PVC

Overall Cable

- Jacket - PVC
- Minimum Average Thickness - 0.60mm
- Outer Diameter - 6.20 ± 0.30mm

Product Uses

- Gigabit 1000 BASE-T; 100 BASE-T; 10 BASE-T (IEEE 802.3)
- 1/16 Mbps Token Ring (IEEE 802.5); 100 VG-AnyLAN

- 100 Mbps TP-PMD (ANSI X3T9.5); 55/155 Mbps ATM
- Voice; T1

Product Support

Downloads

- Download the [technical specifications](#)

Info

About Us
Order History
Where To Buy
More ▾

Service

Contact Us
OEM Solutions
Tech Support
More ▾

Resources

Connector Guides
ConnectXpress
Drivers & Manuals
More ▾

Have A Question?

Get help with [Chat](#)

Call C2G **800.506.9607**



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

