



Copyright FCI


form: A3

TIN LEAD PART NUMBER


D50P82C4GX00	D50P82C6GX00
Gold flash	0.76 μ gold

LEAD FREE PART NUMBER


D50P82C4GX00LF	D50P82C6GX00LF
Gold flash	0.76 μ gold



VIEW F



PC card drilling dimensions(after plating) scale:1.5
(thickness 1.60 ±0.10mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code		surface	tolerance	projection	product family	
-		ISO 1302	ISO 406 ISO 1101		D-SUB	
ltr	ecn no	dr	date	tolerances unless otherwise specified	title	
H	ELX-I-18050	MP	2014/06/23	linear	DELTA-D EUROSTYLE MALE 50	
				angles	RIGHT ANGLED PRESS FIT	
				0°±2°	scale 2:1	
				dr	PESSON	1995/10/17
				engr	MITHUN PAUL	2014/06/23
				chr	ALIAS BABU	2014/06/23
				appd	BIJU K PAUL	2014/06/23
sheet index	revision sheet	H	1		dwg no	sheet 1 of 1
					size	A3
					type	Product Customer Drawing

