



→ Sensing & Control → Automation & Control Solutions → Honeywell.com

HOME ABOUT US PRODUCTS TECHNICAL RESOURCES CUSTOMER SERVICE NEWS AND EVENTS STRATEGIC PARTNERS CONTACT US
Products
Quick Ship Delivery

Honeywell Sensing & Control - Sensors for Test & Measurement

Home

060-6827-03

Print



[View more images](#)

Model U3W Universal Inline Amplifier with 4 to 20 mA Output and 18 to 32 VDC Input

Model: U3W
Order Code: BE125EL,51J
Price: Consult Factory
Lead Time: Consult Factory

[Download Data Sheet](#)



Log In

- [Login to My Account](#)
- [Change Password](#)
- [Forgot Password](#)
- [Forgot UserID](#)
- [Register](#)
- [Need Help?](#)



Search our entire product portfolio by either part number, order code or text

Tips to speed your search

[Overview](#) [Item Specifications](#) [Documentation](#)

Need help contact us

My Cart:

→ [Saved Configurations](#)

Input Types

Strain Gage

Excitation Voltage

3 VDC or 5 VDC @ 70 mA

Power Requirements - Voltages

18 VDC to 32 VDC

Operating Temperature

5 F to 160 F [-15 C to 71 C]

1 of 1

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)

 [Email This Page](#)

© Copyright Honeywell International Inc 2004-2016