

M12-CON-1.0-AWG22-18/0,33-0,82mm²-M



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9981
Specification	M12-CON-1.0-AWG22-18/0,33-0,82mm²-M
HARTING eCatalogue	https://harting.com/21011009981

Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.33 ... 0.82 mm²
Conductor cross-section [AWG]	AWG 22 ... AWG 18
Performance level	1

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated

Commercial data

Packaging size	100
Net weight	0.201 g
Country of origin	Switzerland



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85366990
GTIN	5713140229396
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522