



Commercial status
This Product is Obsolete : NOV 28, 2023

⚠ This Product is Obsolete

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phase
Output voltage	120 V 208 V 3 phase
Input Connection Type	NEMA L21-20P
Number of cables	1
Provided Equipment	Installation guide

Physical

Color	Black
Height	2.52 In (6.4 cm)
Width	2.01 In (5.1 cm)
Depth	264.02 In (670.6 cm)
Net Weight	7.01 Lb(US) (3.18 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Permissible voltage	200...240 V
Max line current	20 A

Output

Maximum Total Current Draw per Phase	20 A
--------------------------------------	------

Conformance

Product Certifications	UL Listed
------------------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

GTIN	731304233121
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.02 In (10.2 cm)
Package 1 Width	17.52 In (44.5 cm)
Package 1 Length	12.01 In (30.5 cm)
Package 1 Weight	7.7 Lb(US) (3.5 kg)

Environmental data

EU RoHS Directive	Not compliant
-------------------	---------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status :	End of commerc. - Block
-----------------------	-------------------------