

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
DS	–


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	02.MAR'09	SC	JK









△1 TABLE 1.

PLUG HOUSING		2	2005247-□
		4	□-368575-□
CAP HOUSING	P/M	2	2005249-□
		4	□-368589-□
	F/H	2	2005248-□
		4	□-368587-□
APPLICABLE PRODUCT		POS	P/N

NOTE:
△1. APPLICABLE CONN. P/N: SEE TABLE 1
2. GENERAL TOLERANCES:±0.3
3. ACCORDING TO IEC 60335-1 4.2 EDITION
-PART MEETS GWT 750°& 850°C.
-MATERIAL MEETS BALL PRESSURE TESTING AT 125°C.
-MATERIAL HAS CTI VALUE OF 250V.

368590-1	NATURAL
P/N	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±–
1 PLC ±–
2 PLC ±–
3 PLC ±–
4 PLC ±–
ANGLES ±–

MATERIAL: PA66, UL94V-2

FINISH: –

DWN: SC KIM
CHK: BW KANG
APVD: JK SONG
PRODUCT SPEC: 108-61106
APPLICATION SPEC: –
WEIGHT: –

Tyco Electronics
AMP KOREA
Kyungsan, Korea

NAME: PDL 2P DBL PLATE 3.96mm (GWT)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C– 368590	–

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV A

Downloaded from Arrow.com.