

PART NUMBER	ENGINEERING NUMBER	FINISH LENGTH
1200690278	888J31E41M150	49.22' +24.5"-0 [15M +0.62 -0]

FRONT VIEW – FEMALE M12




1-WHITE
2-BROWN
3-GREEN
4-YELLOW
5-GREY
6-PINK
7-BLUE
8-RED

FRONT VIEW – MALE M12




1-WHITE
2-BROWN
3-GREEN
4-YELLOW
5-GREY
6-PINK
7-BLUE
8-RED



CUSTOMER PRODUCTION APPROVAL
APPROVED BY:_____
DATE:_____
MUST BE SIGNED AND RETURNED BEFORE PRODUCTION WILL BEGIN.

SALES DRAWING



WIRING

NOTES:

MECHANICAL
M12
INSERT: BLACK PUR
CONTACT: GOLD/NICKEL OVER COPPER ALLOY
COUPLING NUT: NICKEL PLATED BRASS
MOLDED BODY: BLACK PUR
CABLE
TYPE: 24 AWG 4 PAIR CONDUCTORS CP (TP) GRAY PUR JACKET
WRAP LABEL: MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE

ELECTRICAL
FACE
OPERATING TEMP.: -20°C TO +70°C
VOLTAGE: 30V
AMPERAGE: 2A

REV	DESCRIPTION
A	INITIAL RELEASE EC NO: IPG2013-1315 DRWN: BARDEN 2013/02/25 CH'KD: BWOODMAN APPR: BWOODMAN 2013/05/13

QUALITY SYMBOLS
▼=0
Ⓒ=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±0.13	±.010
1 PLACE	±0.25	±.020
ANGULAR ±.5°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: INCH ONLY
SCALE: NTS
DESIGN UNITS: INCH
THIRD ANGLE PROJECTION

DRAWN BY: BARDEN DATE: 2013/02/25
CHECKED BY: BWOODMAN DATE: 2013/03/08
APPROVED BY: BWOODMAN DATE: 2013/05/13

TITLE: MICRO-CHANGE ASSEMBLY 8P M/MFE ST/90 24/4P PUR SHIELDED

MOLEX INCORPORATED

MATERIAL NO.: SEE CHART
DOCUMENT NO.: SD-120069-019
SHEET NO.: 1 OF 1
SIZE: B

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Downloaded from Arrow.com.