



**Part Number :** [1300080353](#)

**Product Description :** Mini-Change C-Size Single-Ended Cordset, 9 Poles, Female (90°) to Pigtail, 16 AWG, PVC Cable, 3.66m (12.0') Length

**Series Number :** 130008

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 309001A01F120

---

## Documents and Resources

### Drawings

[1300080353 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 9 Poles, Female (90°) to Pigtail, 16 AWG, PVC Cable,3.66m (12.0') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Single Ended
UPC	78678844138

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	16.26mm (.640")
Cable Length	3.66m (12.0')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Material - Connector Body	PVC
Material - Contact	Brass
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1596.110/g
Orientation	90° to Pigtail
Poles	9
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	STOOW
Wire Size (AWG)	16

---

This document was generated on Dec 26, 2025