



BSCH0010050512NJCP

Search by : [Part Number](#) [Characteristics](#) [Cross reference](#)



MP ?

Multilayer-STD

- Series Pdf
- RoHSREACHCoC
- ICP Report

Product detail	
Structure	Multilayer
L(mm) ±	1.0±0.10
W(mm) ±	0.5±0.1
T(mm) ±	0.5±0.1
Size Code (JIS/EIA)	1005/0402
Inductance(nH)	12
Unit	nH
Tolerance(±%)	5
Test Frequency(L)	100 MHz,200 mV
Q Min	8
Test Frequency(Q)	100 MHz,200 mV
SRF(MHz)Typ	3000
RDC(Ω)Max	0.28

Operating Temperature

−55°C~125°C(Including self - temperature rise)

Part Numbering


Dimensions

Packing

Recommended Pattern

Electrical Characteristics

S Parameter



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology
- Certificates & Awards

Investor

- Financial Information
- Corporate governance
- Stakeholder Contacts

News

- Media Center
- New Products
- Events
- Product Notices

Contact Us

- Contact Info
- Contact Form
- Join Chilisin

- Terms of Use
- Privacy policy
- Sitemap



Copyrights © 2018. Chilisin. All rights reserved.