



MN62-K True RMS MultiMeter with **FREE** Voltage Detector

Compact True RMS multimeter includes a free Non-contact Voltage Detector (NCV)! Ideal for troubleshooting appliances, electrical wiring, automotive repair and electronic devices.



Features

Model MN62 True RMS MultiMeter

- True RMS for accurate readings of noisy, distorted or non-sinusoidal waveform
- VFC Low pass filter for accurate measurement of variable frequency drive signals
- 10 functions including Frequency and Capacitance
- Built-in non-contact voltage detection with audible beeper indication
- CAT III-600V category safety rating
- Complete with test leads and two AA batteries

Model DV23 AC Voltage Detector

- Safely determine if wires are hot or not
- Non-Contact AC Voltage detection from 50 to 600V, 50/60Hz
- Audible and visual red LED light indicator
- Convenient built-in pocket clip
- Suitable for testing AC outlets, power cords and branch circuits
- CAT IV-600V category safety rating
- Dims/Wt: 6.25x1" (159x25mm) / 1.5oz (42g)
- Complete with two AAA batteries

MN62 Specifications

Display count	4000 count backlit LCD	
DC/AC Voltage	40.00mV, 400.0mV, 4.000V, 40.00V, 400.0V, 600V	DC: $\pm(0.5\%+2d)$, AC: $\pm(1.0\%+3d)$
DC/AC Current	40.00mA, 400.0mA, 4.000A, 10.00A	DC: $\pm(0.7\%+2d)$, AC: $\pm(1.0\%+3d)$
DC/AC μ A	400.0 μ A, 4000 μ A	
Non-Contact Voltage (NCV)	100 to 600V AC (audible beeper)	
Resistance	400.0 Ω , 4.000k Ω , 40.00k Ω , 400.0k Ω , 4.000M Ω , 40.00M Ω	
Frequency	9.999Hz to 9.999MHz	
Capacitance	9.999nF, 99.99nF, 999.9 μ F, 9.999mF, 99.99mF	
Continuity/Diode	Yes	
Dimensions/ Weight	(175 x 80 x 48.5mm)/ 350g (includes batteries)	

Ordering

MN62-K True RMS MultiMeter with Free Voltage Detector



UL listed and CAT IV-600V - DV23 Voltage Detector
ETL listed and CAT III-600V - MN62 TRMS MultiMeter
UPC Code: 793950386224