

CAT. NO. & DIMENSIONS

(NOTE4)	NO. OF CONTACTS (n)	CAT. NO. (NOTE2)	DIMENSIONS (NOTE3)		
			E MAX.	F ± 0.3	G ± 0.1
	4	HFW4R-1/2STE5LF	30.4	24	—
	5	HFW5R-1/2STE5LF	30.4	24	—
	6	HFW6R-1/2STE5LF	30.4	24	—
	7	HFW7R-1/2STE5LF	30.4	24	—
	8	HFW8R-1/2STE5LF	30.4	24	—
	9	HFW9R-1/2STE5LF	30.4	24	—
	10	HFW10R-1/2STE5LF	30.4	24	—
	11	HFW11R-1/2STE5LF	30.4	24	—
	12	HFW12R-1/2STE5LF	30.4	24	—
	13	HFW13R-1/2STE5LF	30.4	24	—
	14	HFW14R-1/2STE5LF	30.4	24	—
	15	HFW15R-1/2STE5LF	38.4	32	28.4
	16	HFW16R-1/2STE5LF	38.4	32	28.4
	17	HFW17R-1/2STE5LF	38.4	32	28.4
	18	HFW18R-1/2STE5LF	38.4	32	28.4
	19	HFW19R-1/2STE5LF	50.4	44	40.4
	20	HFW20R-1/2STE5LF	50.4	44	40.4
	21	HFW21R-1/2STE5LF	50.4	44	40.4
	22	HFW22R-1/2STE5LF	50.4	44	40.4
	23	HFW23R-1/2STE5LF	50.4	44	40.4
	24	HFW24R-1/2STE5LF	50.4	44	40.4
	25	HFW25R-1/2STE5LF	50.4	44	40.4
	26	HFW26R-1/2STE5LF	50.4	44	40.4
	27	HFW27R-1/2STE5LF	50.4	44	40.4
*	28	HFW28R-1/2STE5LF	50.4	44	40.4
*	29	HFW29R-1/2STE5LF	50.4	44	40.4

CAT. NO.

HFW (n) R - 1 ST E5 LF

SERIES

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE
2. UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING (SMT)

TAPE PACKAGING

LEAD FREE

NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
2. THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED CONNECTOR.
3. SEE PART DRAWINGS FOR DIMENSIONS E~G.
4. PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK.

mat'l. code				surface 58/ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection		product family 58NF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm		title			
A	J06-0044	H.T	2/7/06	angles linear				mm		CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONN. (Cat.No. HFW__R-1/2STE5LF)			
B	J06-0413	H.T	10/4/06					scale X					
				dr				FCJ		dwg no sheet 1 of 1 size			
				enrg						JSA 97081 A4			
				chr						type Product Customer Drawing			
				appd									
sheet index		revision B		sheet 1								Rev. B	

SC-HFWR02 JSA95923 97082 97083
form: A4

1

2