



Part Number : [1300850366](#)

Product Description : Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 16/8 SOW, 28.96m (95.0') Cord Length with Flying Leads

Series Number : 130085

Status : Active

Product Category : Electrical Reels

Engineering Part Number : 92681

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Electrical Reels
Series	130085
Description	Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 16/8 SOW, 28.96m (95.0') Cord Length with Flying Leads
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 3R
NEMA Configuration	N/A
Product Name	POW-R-MATIC
Type	Cable Reel
UPC	78678879281

Agency

CSA	LR29921
-----	---------

Electrical

Current - Maximum per Contact	6.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock

Cord Length	28.96m (95.0')
Cord Type	16/8 SOW
Depth	0.58m (22.750")
Drum Lock	Ratchet
Duty	Heavy
Guide Arm	Option Available
Height	0.59m (23.38")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	Rigid
Number of Conductors	8
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	3.2kg (7.0 lb)
Width	466.90mm (18.38")
Wire Size (AWG)	16

This document was generated on Apr 27, 2026