# Specification Sheet

Part Number: T40R9C2



Engineered and manufactured for maximum performance and quality.

Made from 100% high-quality plastic to ensure efficient recycling.

Inside serration for a strong grip onto bundles.

Easy application either manually or with a tensioning tool.

Bent tail allows for simpler insertion.

Cable Tie, 8" Long, UL Rated, 40lb Tensile Strength, PA66, Natural, 100/pkg

| | |
|---|---|
| Article Number | 112-04019 |
| Type | T40R(U) |
| Color | Natural (NA) |
| Quantity Per | pack |
| Product Description | T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. |
| Short Description | Cable Tie, 8" Long, UL Rated, 40lb Tensile Strength, PA66, Natural, 100/pkg |

Downloaded from Arrow.com.

| | |
|---|---|
| Global Part Name | T40R(U)-PA66-NA |
| Minimum Tensile Strength (Imperial) | 40 |
| Minimum Tensile Strength (Metric) | 180 |
| Length L (Imperial) | 8.30 |
| Length L (Metric) | 210.82 |
| Identification Plate Position | none |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Variant | Inside Serrated |
| Width W (Imperial) | 0.16 |
| Width W (Metric) | 4.0 |
| Bundle Diameter Min (Imperial) | 0.06 |
| Bundle Diameter Min (Metric) | 1.5 |
| Bundle Diameter Max (Imperial) | 2.17 |
| Bundle Diameter Max (Metric) | 55.0 |
| Thickness T (Imperial) | 0.045 |

Downloaded from Arrow.com.

| | |
|---|---|
| Thickness T (Metric) | 1.15 |
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V-2 |
| Halogen Free | Yes |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor Use Only |
| Plenum Rating | AH-2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL 62275 |
| UL Recognized (US) | Yes |
| UL Listed (US and Canada) | Yes |
| UL Recognized (US and Canada) | Yes |

Downloaded from Arrow.com.

| | |
|---|---|
| UL Listed (US) | Yes |
| Package Quantity (Imperial) | 100 |
| Package Quantity (Metric) | 100 |
| Customs Number | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.



Downloaded from Arrow.com.