



Catalog No. HS4-30-4

Description: HVYWALL HTSHK 3:1 BLK 4-3/0 48IN

UPC No 786210872056

Home > Connectivity & Grounding > Shrink-Kon > Heat shrinkable tube

Heavy-Wall Heat-Shrinkable Tubing for Cable Range 4 - 3/0 AWG, Expanded Diameter 1.1 Inch, Length 48 Inch, 600 Volt, 90 Degrees Continuous Use, Cross-Linked Polyolefin with Thermoplastic Adhesive Liner, Black

Descriptors	
Category	Heat shrinkable tube
Special Features	Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
Specifications	
Voltage Rating	600 V
Color	Black
Classifications	
Brand Name	Shrink-Kon
Dimensions	
Length	48 in
Compliance and Certifications	
RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant
Additional Information	
ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	27.94 mm
Inner diameter before heat-shrink	1.1 inch
Inner diameter after heat-shrink	8.89 mm

ETIM	EC000217 Shrink tubing
Inner diameter after heat-shrink	0.35 inch
Nominal diameter inch	Other
Wall thickness after shrinking	3.048 mm
Wall thickness after shrinking	0.12 inch
Length	1.2192 m
Length	4 ft
Operation temperature	-55-+110 °C
Operation temperature	-67-+230 °F
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y