



Combination Pliers

Wire Strippers and Dismantling Tools

Gripping Pliers

Grip Pliers

Circlip Pliers

Carpenters' Pincers

Concreters' Nippers

Cutting Pliers

Pipe Wrenches and Water Pump Pliers

Special Pliers and Tool Lamp

Precision Tweezers

Cable and Wire Rope Shears

Bowden Cable Cutter

Cable Cutters

Cable Cutters

Cable Shears

Cable Shears

Cable Shears

Cable Shears with telescopic handles

Cable Shears with twin cutting edge

Cable Shears with telescopic handles

Electricians' Shears

Wire Rope and Cable Cutters

Wire Rope Shears

Crimping Pliers

Crimp Assortments

Cable Connectors

Insulated Tools

Tools with tethering

Control Cabinet Keys

Tool Kits

Tool Bags / Cases

Sales Aids

spare parts

Symbols

Orbis products

Rennsteig products

[Products](#) > [Cable and Wire Rope Shears](#) > [Cable Shears](#)



95 11 165 Cable Shears



Technical details

Description

No.	95 11 165
tool	burnished
Handles	plastic coated
Style	1
Cutting capacity copper cable, multiple-stranded (diameter)	19/32 Ø Inch 15 Ø mm
Cutting capacity copper cable, multiple-stranded	1 31/32 in² 50 mm²
AWG	1/0
Length	6 1/2 Inch 165 mm
Net weight	0,474 lbs 215 g

technical change and errors excepted



Cable Connectors
Carpenters' Pincers
Circlip Pliers
Combination Pliers
Concreters' Nippers
Control Cabinet Keys
Crimp Assortments
Crimping Pliers
Cutting Pliers
Grip Pliers
Gripping Pliers
Insulated Tools
Pipe Wrenches and Water Pump
Pliers
Precision Tweezers
Sales Aids
spare parts
Special Pliers and Tool Lamp
Tool Bags / Cases

Making Combination Pliers

Tell Us About Our Tools!
Testimonials

Product Videos
Awards / Contests

About us

KNIPEX in Germany
History
Quality in every detail
Visit us...