



Part Number : [192030092](#)
Product Description : Krimptite Temp-Term Ring
Tongue Terminal for 12-10 AWG Wire, Stud Size 6
(M3.5), Mylar Tape Carrier
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : C-S-128-06T



Documents & Resources

Drawings
[192030092 sd.pdf](#)

3D Models and Design Files
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	800753050013

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.364/g
Packaging Type	Adhesive Tape on Reel
Stud Size	6 (M3.5)
Wire Size (AWG)	10, 12

Wire Size mm ²	2.70-6.60
---------------------------	-----------

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270088</u>
Mini-Mac Applicator	<u>638851000</u>

This document was generated on Sep 11, 2025