Part Number : 1202470001
Product Description : M8 Signal, MPIS Passive Distribution Box, Top-Mount, 4 Ports, PNP LED Indicators, WSOR Home Run Cable, 5.0m (16.4') Length
Series Number : 120247
Status : Active
Product Category : Passive Distribution Boxes
Engineering Part Number : BEB401P-FBW-05



Documents and Resources

Drawings

1202470001_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	120247
Description	M8 Signal, MPIS Passive Distribution Box, Top-Mount, 4 Ports, PNP LED Indicators, WSOR Home Run Cable, 5.0m (16.4') Length
IP Rating	IP67
Product Name	M8 Signal,Nano-Change (M8),MPIS
UPC	889056129466

Agency

UL	E152210

Electrical

Current - Maximum per Contact	6.0A per module, 2.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC
Wiring Configuration	Single I/O per Port

Physical

Bus I/O	N/A
Cable Connector Orientation	Straight
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	A-Coded
LED Indicator	PNP Sensors
Material - Cable Jacket	TPU

Downloaded from Arrow.com.

Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	469.800/g
Orientation	Top-Mount
Poles	3
Poles (wired)	3
Ports	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	TPU (WSOR)

Downloaded from Arrow.com.